Industrial Pumps

Easy-to-Service Mono-Block Pumps



An Innovative New Hydra-Cell Design to Lower Maintenance Costs and Reduce Downtime

Mono-Block Features:

- Easy access, one-piece cartridge style check valves for servicing without disassembly of pump or removal of plumbing
- Kel-Cell® diaphragm position control standard on all Mono-Block pumps
- Left and right inlet and outlet ports for easy plumbing installation
- 316 Stainless Steel and brass pump heads available
- NPT or BSPT inlet and outlet ports available
- Diaphragms available in Buna, Viton, Neoprene and EPDM
- · Variety of drive options available






Mono-Block Pumps for Ease of Installation & Service

Mono-Block style pumps allow easy access to the cartridge style valve assemblies

The latest improvement to the design superiority and operational excellence of Hydra-Cell pumps, Mono-Block helps you avoid critical downtime while cutting service and maintenance costs. Now available on the Hydra-Cell D03, M03, G03, and G13 series of pump, the Mono-Block pump head combines the traditional valve plate and manifold into a single component. Valve assemblies are accessible by removing the valve plugs in the Mono-Block without disturbing the plumbing, making disassembly of the pump unnecessary.



Mono-Block Components:



Pump Configurations:

Model	Description
D03	Shaft-driven (1/2-inch NPT ports)
M03	Close-couple to NEMA 56C motor (1/2-inch NPT ports)
G03	Shaft-driven (1/2-inch BSPT ports)
G13	Close-couple to IEC 90B5 motor (1/2-inch BSPT ports)

Specifications:

Maximum Pressure (Metallic Heads):	1000 PSI (70 bar)	
Capacity @ 1000 PSI Maximum Pressure:		
Models D/G-03-X (Kel-Cell)*	1750 rpm	3.0 gpm (11.3 lpm)
Models D/G-03-E (Kel-Cell)*	1750 rpm	2.2 gpm (8.3 lpm)
Delivery @ 1000 PSI Maximum Pressure:		
Models D/G-o3-X (Kel-Cell)*	584 revs/gallon (155 revs/liter)	
Models D/G-03-E (Kel-Cell)*	795 revs/ga	allon (204 revs/liter)
Maximum Inlet Pressure:	250 PSI (17 bar)	
Maximum Temperature (Metallic Heads):	250°F (121	°C)

^{*}Mono-Block Kel-Cell® available in X and E models only. (Kel-Cell® is a registered trademark of Wanner Engineering, Inc.)

Choice of Materials:

Pump Head:	Brass or 316 Stainless Steel	
Diaphragm & O-ring:	EPDM, Viton®-XT, Neoprene or Buna-N-XS	
Valve Seat:	17-4 PH Stainless Steel, 316 Stainless Steel or	
	Hastelloy®C	
Valves:	17-4 PH Stainless Steel (machined), 17-7 PH	
	Stainless Steel, Nitronic 50 or Hastelloy®C	
Valve Springs:	Elgiloy® (exceeds SST grade 316), 316 Stainless	
	Steel or Hastelloy®C	
Spring Retainers:	Kynar® or Polypropylene	



Minneapolis, MN 55403 USA Phone: 612-332-5681 Fax: 612-332-6937 Toll-Free Fax (USA): 800-332-6812 Email: sales@wannereng.com www.Hydra-Cell.com



Units 8 & 9, Fleet Business Park Sandy Lane Church Crookham, Hampshire GU52 8BF, England Phone: +(44) 01252 816847 Fax: +(44) 01252 629242 Email: sales@wannerint.com www.WannerInt.com



Flat A, 21/F, Chatham Commercial Building 399 Chatham Road North Hunghom, Kowloon, HONG KONG Phone: +(852) 3428-6534 Fax: +(852) 3188-9145 Email: sales@wannerpumps.com www.WannerPumps.com